

## Conductor markers CLI C 1-9 GE/SW 300-319 2-PAG RL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



**CLI C** conductor markers are fitted to unconnected conductors. Four different sizes are available to conductor cross-sections from 0.5mm<sup>2</sup> to max. 70mm<sup>2</sup>. The markers are already printed and ready for use. Individual markings can be created simply by combining the individual markers.

- Closed markers, secure and adjustable on unconnected cables
- Special flexible bellow profile ensures a wide application range
- Fast and easy to fit – in next to no time
- Compatible accessories take the strain off marking tasks
- Permanent high-quality markings
- Best contrast for optimum legibility

### General ordering data

Order No.	<a href="#">1878260300</a>
Type	CLI C 1-9 GE/SW 300-319 2-PAG RL
Version	Conductor markers, 9 x 4.2 mm, PVC, soft, without Cadmium, Colour: Yellow
GTIN (EAN)	4032248469895
Qty.	1,000 pc(s).

## Conductor markers CLI C 1-9 GE/SW 300-319 2-PAG RL

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Length	9 mm	Width	4.2 mm
Height	5.1 mm	Depth	5 mm
Net weight	0.156 g		

### Markings

Cadmium	No	Colour	Yellow
Colour of printing	Black	Conductor O.D.	3 - 5 mm
Conductor cross-section, max.	4 mm <sup>2</sup>	Conductor cross-section, min.	1.5 mm <sup>2</sup>
Halogen	Yes	Insulation cross-section, max.	5 mm
Material	PVC, soft, without Cadmium	Material colour according to resistance code	4
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Pin can be written (STI)	No
Printed characters	Numbers	Printing method	Laser print
Type of printing	Standard	UL 94 flammability rating	V-0

### Classifications

ETIM 2.0	EC001530	ETIM 3.0	EC001530
UNSPSC	44-12-17-08	eClass 4.1	24-19-02-19
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

### Product information

Product description	CLI paged markers combine CLI C markers with consecutive numbering. (two of each number, e.g. 10, 10, 11, 11 etc.)
---------------------	-----------------------------------------------------------------------------------------------------------------------

### Approvals

Approvals	
ROHS	Conform

**Conductor markers**  
**CLI C 1-9 GE/SW 300-319 2-PAG RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



Product is similar to illustration