HEAVY DUTY GOOSENECK FLEX ARM

95136 24" Long, 1/4-20 Female Both Ends



ARM LENGTH	24" (609.6 mm)
ARM MATERIAL	Steel
OUTSIDE DIAMETER	.695"
INSIDE DIAMETER	.325"
LOAD RATING	Max Load @ 90 Degrees:
	1.5 pounds
FEEL	Heavy Duty, Feels Stiff
MOUNTING STYLE	Female Threads, or
	Male Thread Conversion Kit included with single use tube of Loctite and Male Studs (2)
TOP FITTING	1/4-20 UNC Female Thread
BASE FITTING	1/4-20 UNC Female Thread
COVERING SLEEVE	PVC, Matte Black



800-346-0761

222 Cessna Street
Watertown, SD 57201
sales@moffattproducts.com

