## Auto Focus Mighty Scope 2M USB Digital Microscope • Product # 26700-203



Rating: \*\*

Product #: 26700-203

Overview: Mighty Scope 2M Auto Focus USB Digital Microscope 10x-50x, 200x magnification with white LED illumination, Metal Stand and Image Capture & Measurement Software. Can also be operated in manual mode. 30-day money back guarantee. Two year manufacturer's warranty.

Specs

## Auto Focus Mighty Scope 2M USB Digital Microscope

Image Sensor Color CMOS

Effective Pixels 2.0M

Signal Output USB 2.0

Video Format AVI

Magnification 1 to 80X, 200x

**Gain Control** Automatic

**Snap Shot Mode** Hardware & Software controls

White Balance Automatic

**Power Source** 5VDC through USB port

O/S Windows XP, Vista & 7

Power Consumption 110mA (AVG)

Auto Focus Mighty Scope 2M USB Digital Microscope

**LED Lighting** 4 Brightness controllable LEDs

At 10x, 112mm

Working Distance At 20x, 42mm At 30x, 19mm

At 40x, 8.5mm

Length: 109mm Diameter: 39mm

**Dimensions** Cable length: 1.99M (6.54ft)

Metal Stand: Base: 200mm x 200mm

Pole Height: 300mm

Weight 113g

Mighty Scope Autofocus 2M

Metal Stand

Package Contents Image capture & measurement software

Metal Stand Manual

Warranty

 $The \ Auto \ Focus \ Mighty \ Scope \ 2M \ USB \ Digital \ Microscope \ comes \ with \ a \ two \ year \ warranty \ against \ any \ manufacturing$ 

defects.

30-Day Money-Back Guarantee We want you to be fully satisfied with every item that you purchase from Aven. If you are not satisfied with an item that you have purchased, you may return the item within 30 days of delivery for a full refund of the purchase price. Items must

be returned in original packing and condition. RMA # is required.