

TL-130A

Model TL-130A **General Purpose DMM Kit**

If you need only one basic accessory kit for your meter, this is the one. Attach probes or clips to the sheath plug to complete your test. Soft, flexible silicone leads make movement easy. Kit is voltage and current rated for either electronic or electrical applications.

- All components compliant to IEC61010-2-031
- Silicone Lead Wire length 60" (1.5m)

model

CATIII

CATIII

CATIII

CATI

12A

36A

20A

3A

TL-130A

1000V

1000V

1000V

300V

■ Tri-fold Velcro Pouch

4mm Straight to Right-Angle

Probe Bodies w/Ø2mm Tip

Silicone Leads, 1.5m

Alligator Style Clips

Alligator Clips

Features



Model CP-3

DC/AC Current Clamp

- Converts any DMM to a current clamp
- Measures current without disconnecting circuit under test
- Measures to 400A DC or AC
- Outputs I mV per Amp, operates on 2V range of any DMM

Multimeter Accessories



TL-50

Specifications

	CP-3		
(Accuracy specif	ied at 18° to 28°C)		
Current Range	2A to 400A, DC or AC		
Frequency Response (AC)	50 Hz - 400 Hz		
Accuracy	\pm (2% reading + 2A)		
Input Resistance	10k $Ω$ min.		
Maximum Conductor Size	1.1" (30mm)		
Power Requirement	9V battery, NEDA 1604		
Battery Life	100 hr typical		
Operating Temperature	0° to 40°C, <70% RH		
Storage Temperature	-20° to + 70°C. <80% RH		

<u>model</u>

Model TL-50 Maxi-Pro DMM Kit

Complete accessory kit for all your DMM testing needs. Includes soft, flexible silicone lead wire easy movement and Tri-Fold Velcro Pouch for convenient storage.

- All components compliant to IEC61010-2-031
- Silicone lead wire length 60" (1.5m)
- Tri-fold Velcro Pouch

Features

Model TL-10 **SMD Probe Kit**

Extended, slim-line probe body for easy reach. Use with small SMD components or general purpose test points. Includes soft, flexible silicone lead wires for easy movement and clear, PVC Pouch for convenient storage.

- All components compliant to IEC61010-2-031
- Silicone Lead Wire length 60" (1.5m)
- **Clear PVC Pouch**

0000
9
PR-6506

Model PR-650A **RF DMM Probe**

All purpose RF demodulator probe, usable with most DMMs. Allows a DMM to measure sine wave AC signals: IVeff=IVDC Features light weight design.

	N.A	
TL-50		
1000V	CATIII	I2A
1000V	CATIII	36A
1000V	CATIII	6A
1000V	CATIII	20A
300V	CATI	3A
42V (1000V)		36A
42V (1000V)		36A
	1000V 1000V 1000V 1000V 300V 42V (1000V)	TL-50 1000V CATIII 1000V CATIII 1000V CATIII 1000V CATIII 300V CATIII 42V (1000V)

PR-28A

Model PR-28A 40 kV High Voltage DMM Probe

If the voltages you need to measure are above the specifications of general purpose probes, B+K Precision has a higher voltage probe for you.

Featu	res		m	odel
		TL-	10	
4mm Straight to	Right-Angle			
Silicone Leads, I	.5m	1000V	CATIII	12A
Extended Tip Pro	be Bodies	1000V	CATIII	20A

Specifications

	PR-650A
Bandwidth	100kHz to 650MHz
Accuracy	±1dB (100kHz-300MHz)
	±3dB (300MHz-650MHz)
Input Voltage	100V
HF Voltage	35Veff
Actuating Voltage	350mV
DMM Input	
Impedance	10ΜΩ
Input Capacitance	8pF
Cable Length	48" (1.2m)

Features model PR-28A 1000ΜΩ x1000 Attenuation Impedance Voltage (AC) 20kV Accuracy (AC & DC) ±3% Voltage (DC) 40kV Cable Length 48" (1.2m)

60Hz



Bandwidth

Multimeter Accessories

Replacement Test Leads



TL-2A



TL-3



TL-1



TL-4



Model TL-2A

Deluxe Test Lead Sets

- IEC61010 1000V CATIII Rating
- Silicone Lead Wire length 60" (1.5m)
- Black Alligator Clip included
- ■Threaded tips fits TL-3
 Accessory kit items

Model TL-3

Probe Accessory Kit

- Threaded accessories to fit TL-2A probes – Black and Red pairs (except for alligator clip)
- Alligator clip, Red only
- Spring hook clips
- 4" Sharp extension tips to reach tight test points
- No. 10 Spade lugs

Model TL-100A

UL Listed Probes w/PVC wire

- IEC61010 600V CATIII Rating
- UL Listed
- Highly flexible PVC lead wire, 40" (1.0m)
- Black and Red Alligator clips

Model TL-1 Model TL-4

Economical replacement test leads. TL-1 has safety shrouded banana plugs. TL-4 has un-shrouded banana plugs.

- 1500V 3A ratings
- PVC lead wire, 40" (1.0m)
- Black and Red Alligator clips

TL-8

Surface Mount Tweezers

- Two conductor leads
- 400V rms, IA

Test Accessory Pairs

(Supplied as Black & Red Pairs)

AD-101

Banana Plug Adapter Set

■ 42V (1000V) 36A Rating w/trained user

CC-104

Silicone Lead Set

- Highly Flexible Silicone Jacket
- 4mm Sheathed Straight to Right-Angle Plugs
- 60" (1.5m) length
- IEC61010 1000V CATIII 12A Rating

TIP-102

Insulated Alligator Clip Set

■ IEC61010 1000V CATIII 20A Rating

TIP-104

Insulated Space Lug Set

■ 42V (1000V) 36A Rating w/trained user

TIP-110

Very Fine Tip Probe Set

- Extended length w/SS tip
- IEC61010 1000V CATIII 20A Rating

TIP-125A

Alligator Style Clip Set

- Rigid clip body
- IEC61010 1000V CATIII 20A Rating

TIP-127

Flexible Pincer Clip Set

- **■** Flexible shaft
- IEC61010 1000V CATIII 6A Rating

TIP-128A

Insulation Piercing Clip Set

- Wires up to .145" diameter
- 60VDC/30VAC, 6A Rating

TIP-129

Standard Alligator Clip Set

■ IEC61010 300V CATI 3A Rating

TIP-130

Probe Body Set

- ø2mm Probe Tip
- IEC61010 1000V CATIII 36A Rating

TL-140

5-Way Test Clip Set

- 5-Way Communication Clip
- 60" (1.5m) Silicone Leads



AD-101



















Features model

	PR-60			
Bandwidth	25MHz (-3dB)			
Attenuation Ratio	x10/x100			
Accuracy	±2%			
Rise Time	14 ns			
Input Impedance	4MΩ/10pF			
	each side to ground			
Input Voltage				
Max. Differential	±700V (DC+Peak AC)			
Max. Common Mode	±700V (DC+Peak AC)			
Output Voltage				
Max. Amplitude	±7V (into 2kΩ load)			
Offset (Typical)	≤ ±5mV, -10°to 40° C			
Noise (Typical)	1.5 to 2mV			
Source Impedance	IΩ @ IkHz			
	8Ω @ 1MHz			
CMRR				
50Hz	86 dB			
20kHz	66 dB			
200kHz	56 dB			
Probes	Spring Hooks (B/R)			
Length of Input Lines	18" (45cm)			
Operating Temperature	14° to 104°F (-10° to 40°C)			
Power Requirements	4 x AA Cells			
Certification	IEC61010-1 CATIII			



Model PR-60
Active Differential Probe

Allows safe and accurate floating measurements with your standard analog or digital oscilloscope. Switchable between x10 and x100 attenuation. Unit includes black and red probes and yellow protective rubber jacket.

General Purpose Probes

B+K Precision offers a complete line of oscilloscope probes to enhance the versatility of your unit. Both fixed attenuation and switchable from 90 to 250 MHz are available. Each probe includes a full accessory kit with a Sprung Hook, Replacement Tip and BNC Adapter.

- Models PR-37AG and PR-37AR have REF position on switch for easy ground referencing.
- All models compliant to IEC61010-2-031





PR-2000

High Voltage Probes

If the voltages you need to measure are above the specifications of the general purpose probe, B+K Precision has higher voltage probes for you.

■ PR-2000 — 2 kV

■ PR-4000 — 4 kV

■ PR-55 — 10 kV

■ PR-15K — 15 kV

Specific	ations								mo	dels
	PR-33A	PR-37AG	PR-37AR	PR-150	PR-46A	PR-100A	PR-2000	PR-4000	PR-15K	PR-55
Attenuation	x1/x10	x1/x10/REF	x1/x10/REF	x1/x10	x1/x10/REF	x100	x100	x100	x1000	x1000
Input Impedance										
R(MΩ)	1/10	1/10	1/10	1/10	1/10	100	100	50	500	100
C(pF)	46/16	100/15	100/15	45/12	90/14	6.5	5	5	3	I
Bandwidth (MHz)	15/90	6/150	6/150	25/150	10/250	250	200	100	5	50
Voltage (VDC+ACmax)	600	600	600	600	600	1,200	2,000	4,000	15,000	10,000
Compensation (pF)	1035	1035	1035	1030	1035	1035	1030	1030	_	1030
Cable Length	48" (1.2m)	40" (1.0m)	80" (2.0m)							
Body Color	Black	Gray	Red	LtGray	Gray	Black	Red	Red	Red	Yellow


PR-150

Oscilloscope Accessories

Model PR-32A

Demodulator Probe

All purpose demodulator probe, usable with most oscilloscopes. Features light weight design and 48" (1.2m) coaxial cable.





PR-32A

CC-410

model



CC-110

Models CC-41A and CC-150 BNC Cable Assemblies

Standard BNC cable assemblies in three convenient lengths. Black, molded strain release boots provides for long-life. RG58C/U cable and 50Ω impedance. CC-110 is a special fully insulated BNC male to male cable assembly. Meets IEC61010 safety standards. Uses highly flexible RG58 Type cable in two meter length. Color: Black.

Model CC-25 BNC / N Type Adapter Kit

The kit contains the most popular In-Series and Between Series BNC and N-type adapters. Solve your hookup problems easily. Bodies are brass, nickel plated with gold plated center contacts.

- Nine BNC and N Type adapters
- 50 Ω impedance
- 500Vrms Rating



Fea	ture	S		models
	CC-41A	CC-150	CC-155	CC-110
Impedance		50Ω		50Ω
Cable		RG58 C/	RG58 Type	
Connectors		BNC male	Insulated BNC male	
Voltage		500Vrms	150V CAT II	
VSWR		≤ 1.2	≤ 1.2	
Cable Length	40"	48"	60"	80"
	(1.0m)	(1.2m)	(1.5m)	(2.0m)





Adapter Legend

		CC-25
a. BNC female to female	e. N female to female	i. BNC female to N male
b. BNC female to N female	f. BNC male to male	
c. N "T" female to male to female	g. BNC "T" female to male to female	



AD-110

Model AD-110 BNC Adapter

Fully Insulated BNC male to 4mm sheathed Jack. Use DMM test leads on BNC female connectors.

- IEC61010-1 500V CAT I
- 50 Ω impedance
- **■** Fully Insulated



Model TE-26 BNC 50Ω Feedthru Termination

Connect 50Ω impedance accessories to $1M\Omega$ impedance instruments.

- **50**Ω impedance
- 2W power

Models CC-21 & CC-130

Special BNC Cable Assemblies

Standard BNC to Alligator clips or Sheathed Stacking Plugs. Model CC-21, Black, molded strain release boots provides for long-life. RG58C/U cable with 50Ω impedance. Model CC-130 with fully insulated BNC male to Sheathed Stacking 4mm plugs. Meets IEC61010 safety standards. Includes highly flexible RG58 Type cable in 2.0 meter length. Color: Black.

eatures model				
	CC-21	CC-130		
Impedance	50Ω	50Ω		
Cable	RG58 C/U	RG58 Type		
Connectors	BNC m to Alligator Clips	Insulated BNC male to 4mmPlugs		
Voltage	500Vrms	150V CAT II		
VSWR	≤ 1.2	≤ 1.2		
Cable Length	40" (1.0m)	80" (2.0m)		



General Purpose Accessories

Features

model

Model PR-50

3 Piece Oscilloscope Probe Kit

If you need a complete range of probe attenuation, then this is the kit for you. It contains three probes - x1, x100, and x1/x10 switchable. They are of the same high quality as B+K Precision standard probes but in one convenient kit. Each probe includes a full accessory offering with Sprung Hook, Replacement Tip, Ground Lead and BNC Adapter. All probe are compliant to IEC61010-2-031.

Model TL-55

Test Lab Starter Kit

For the first time student or new lab technician, here is a complete starter accessory kit. It contains the most commonly used products for instrument hookup - leads, probes, hooks and alligator clips for DMMs,150 MHz x1/x10 switchable oscilloscope probe, BNC cable and BNC adapters - everything you'll need to get started. They are of the same high quality as B+K Precision offers individually but in one fully stocked kit. Get going in your profession with B+K Precision instruments and the convenient Model TL-55, Test Lab Starter Kit. Packaged in plastic box.


Kit Contents		mod	lel
		TL-55	
4mm Straight to Right-Angle Silicone Leads, 1.5m	1000V	CATIII	12A
Probe Bodies w/ø4mm Tip	1000V	CATIII	36A
Fully Insulated Alligator Clips	1000V	CATIII	12A
Sprung Hooks	500V	CATI	3A
150MHz Oscilloscope Probe x1/x10/Ref	600V	CATI	
BNC male to male Cable Assembly, 40" (1.0m)	500Vrms		
BNC Breakout to IC Clip	500Vrms		
Insulated BNC male adapter to 4mm Jacks	500V	CATII	3A
BNC female to 4mm Banana Plugs	500Vrms		
BNC male to 4mm Binding Post Adapter	500Vrms		

Model FP-6

Semiconductor Test Leads

Specialized test lead set for B+K Precision semiconductor testers. Three conductor lead with 4mm banana plugs to mini-IC test clips.

- 3 conductors Yellow, Green and Blue
- 30" (76cm) length










FET Probe Accessories





Model PR-70

Active FET Probe

An Active FET probe enables you to measure high frequency signals on your B+K Precision Spectrum Analyzer. Powered by a 12VDC adapter (included), the probe measures frequencies up to 1GHz with an input impedance of 2pF and 1M Ω . The probe also works on B+K Precision oscilloscopes.

The probe includes a full accessory kit for the most demanding applications. Accessories include: 4 - 0.031 gold measuring tips, 2 - ultra-miniature test clips, 2- miniature test clips, 2- 5cm miniature test leads and 2- 10cm miniature test leads.

Note: Probes 50Ω output impedance requires TE-26 50Ω feedthru terminator when used on $IM\Omega$ input impedance oscilloscopes.



Model TIP-70

Active FET Probe Accessory Kit

Replacement Kit for Active FET Probe.

Items include: 4 - 0.031 gold measuring tips, 2 - ultra-miniature test clips, 2- miniature test clips, 2- 2" (5cm) miniature test leads and 2- 4" (10cm) miniature test leads.

Power Supply Accessories

TL-30

30A Power Supply Cable

- #10 Spade Lug to Large Battery Clips
- 30A rating
- Black and Red pair
- 30" (0.75m) length

TL-5A

5A Banana Plug Power Supply Cables

- 4mm Banana plug to alligator clip
- 5A rating
- Black and Red pair
- 40" (1.0m) length





TL-5A





Carrying Cases

B+K Precision offers padded cases to protect your valuable instruments. Choose an appropriate case to meet your needs.

- Light weight, durable Cordura nylon
- Protects your instruments
- Room to hold your test leads



LC-29B

Specifications models					
	LC-24	LC-28A	LC-29B		
For Models	Mini-Pro® DMM 2405A, 2407A, 2408	Capacitance Meter 830	All handheld DMM except for 5300 series and Mini-Pro® series		
			Component Testers 810B, 815, 875B, 878, 885, 890		
Dimensions	3.75 x 1.5 x 6.75" (95 x 38 x 171mm)	4.63 x 2.5 x 7" (117 x 64 x 178mm)	4 x 2.5 x 8" (102 x 64 x 203mm)		
Weight	1.27oz. (36g)	3.53oz. (100g)	2.47oz. (70g)		
Material	-	1000D Navy Cordura Laminate Laminate to a 3/16" foam padding, trico backing			

	LC-32A	LC-33	LC-40	models LC-210A
For Models	High Voltage Probes	Clamp-on DMM	Function Generators	Oscilloscopes
	HV-44A, PR-28A	312A, 313, 330B	4010A, 4011A	2120B, 2125A, 2126A,
		350B, 367, 369B	4017A, 4040A	2190B, 2522B, 5105A
			Bench Top DMM	Spectrum Analyzers
			2831C	2625, 2630, 2635
Dimensions	17.2 x 3 x 3.5"	5 x 1.75 x 10.5"	11 x 5.5 x 12"	15 x 7.5 x 17.5"
	(437 x 76 x 89mm)	(127 x 44 x 267mm)	(279 x 140 x 305mm)	(381 x 191 x 445mm)
Weight	8.4 oz. (238g)	3.18 oz. (90g)	1.02 lbs. (470g)	2.36 lbs. (1070g)
Material	1000D Navy Cordura Laminate			1000D Navy Cordura
	to a 3/16" foam padding, trico backing			400D nylon packcloth
				inside to help it encompass
				the 1/4" foam padding









LC-33



LC-40

