

Metal Shielded (FTP) RJ45 Connectors rated for stranded & solid CAT 7/6A/6 cable (20-Pack) C20-088L7S-20



- CAT6 / CAT6A / CAT7 RJ45 Connectors made by high-performance shielded housing and the thick gold-plated three-prongs gold-plated contacts ensure fast data transfer speed, reduce pair to pair alien crosstalk, and greatly improve noise immunity at all frequencies.
- Plug Housing is made of flame retardant eco-friendly PC material, with the copper casing with nickle-plated which assure that each crimping without fail.
- The load bar is best for installation. The tail clamp protected support barrel evenly crimped and firm around the cable.
- The RJ45 modular plugs accept 23 to 26 AWG shielded or unshielded cable.
- Our Shielded Modular Connectors rated for stranded & solid CAT 7/6A/6 cable.
- Suitable for CAT6A / CAT7 cables and support POE; Used for CCTV, Routers, Switches, Printers, Hubs, PC, and Servers.
- Our RJ45 ethernet connectors compliant RoSH to ensure reliability and quality assurance.
- Package includes 20 pieces Modular Connectors with 20 pieces load bars.

Due to the overall thickness of the shielded bulk cable, some standard RJ45 connectors will not fit properly. We recommend using our universal CAT 7/6A/6 shielded modular connectors (C20-088L7S-20) or purchase the bundle kit to ensure a correct installation for optimal signal performance

Specifications/Contents:

Model: C20-088L7S-20

Category: Works with CAT 7, 6A, 6 cable

Wire Gauge: Works with 23 to 26 AWG shielded or unshielded cable

Compatible Cable: Works with solid or stranded cable up to 8.0 mm diameter

Quantity: 20 pcs Weight: 0.20 lbs