

Material: Nylon 66 UL 94V-0

Ordering Code:

 $\begin{array}{c|cccc} \underline{\text{CP35}} & & ** & \underline{S} & \underline{\text{001}} & \underline{0} & -\underline{\text{NH}} \\ \hline \underline{\text{0}} & \underline{\text{3}} & \underline{\text{4}} & \underline{\text{5}} & \underline{\text{6}} \end{array}$

- 1 Series No.
- (2) Connector:
- (3) Contact type: S = Receptacle
- (4) Color: 001 = Color Black(5) Option: 0 = Standard
- Λ 6 -NH= Halogen-Free

Circuits		Dimension			
		Α	В		
	2		3.9(.154)		
	4	3.00(.118)	6.9(.272)		
	6	6.00(.236)	9.9(.390)		
	8	9.00(.354)	12.9(.508)		
	10	12.00(.472)	15.9(.626)		
	12	15.00(.591)	18.9(.744)		
	14	18.00(.709)	21.9(.862)		
	16	21.00(.827)	24.9(.980)		
	18	24.00(.945)	27.9(1.098)		
20		27.00(1.063)	30.9(1.217)		
	22	30.00(1.181)	33.9(1.335)		
24		33.00(1.299)	36.9(1.453)		

Halogen-Free RoHS compliant

4				CVILUX CORP			DATE	UNIT: mm / inch	TITLE: 3.00mm PITCH POWER
3				2019.07.05	DRAWN BY:	Sandy	6/11-19	TOLERANCE	CONNECTOR FEMALE HOUSING
2				USSUED	ENGINEER:	Sun	6/19-19	UNLESS OTHERWISE SPECIFIED X ±0.30/.012 X.* ± 1*	- MATERIAL:
\triangle	Sandy	6/11-19	ECNT119143		CHECKED BY:	Eisley	7/04-19	.XX ±0.20/.008 .X* ±	- CUSTOMER: HLO142
SYM	NAME	DATE	REV	/ISIONS	APPROVED BY:	Eisley	7/04-19	.XXX ±0.10/.004 .XX* ±	CUSTOMER: HL0142 F5T0051

瀚荃股份有限公司 CviLux Corporation

DRAWING NO.	CP3589SB	PART NO.	CP3	5**S0	010-	NH
SCALE	3 / 1	SHEET	1	0F	1	