
PRODUCT DATA DRAWING



MATERIAL:

CONNECTORS: 2X SMP FEMALE (1221-4010)

CABLE: FLEXIBLE Ø.047 CABLE (200-70-214)

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: FREQ. RANGE: 50 OHMS DC TO 40 GHz.

MATERIAL: SEE	ENOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0'	UNLESS OTHER	Amphenol WWW.svmicrowave.com				
FINISH: SEE	ENOTES	X°X' ±15' DECIMAL: .X ±.030 .XX ±.010	 ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] ALL DIMENSIONS ARE AFTER PLATING. BREAK CORNERS & EDGES .005 R. MAX. CHAM. 15T & LAST THREADS. 					
SURFACE AREA: N/A		.XXX 1.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DA: SON COMMON CENTERS TO BE CONCENTRIC WITHIN 005 T.I.R. 7) REMOVE ALL BURRS		SMP FEMALE TO SMP FEMALE Ø.047 CABLE ASSEMBLY			
PROPRIETARY								
	IN CONTAINED IN THIS DRAWING OPERTY OF SV MICROWAVE, INC. TION IN PART OR AS A WHOLE RITTEN PERMISSION OF INC IS PROHIBITED.	THIRD ANGLE PROJECTION	DRAWN:	SRM 01/25/22	SIZE DWG. NO.			
ANY REPRODUCTION IN I			CHECKED:	SEE PDM	B		7012-	1926
SV MICROWAVE, INC IS P			APPROVED:	SEE PDM	SCALE:	6:1		SHEET 1 OF 1

REVISION HISTORY							
REV	DESCRIPTION	DATE	TE APPROVED				
01	PRELIMINARY	01/22					
02	PRELIMINARY	04/22	SEE PDM				