
PRODUCT DATA DRAWING



2.92MM BLKHD STR. FEMALE

APPROVED:

MATERIAL:


CONNECTORS: 2.92MM STR. MALE (SF1511-60069) 2.92MM BULKHEAD STR. FEMALE (SF1521-60045)

CABLE: CONFORMABLE Ø.047 CABLE

SHRINK TUBING: M23053/5

PERFORMANCE:

| IMPEDANCE: | 50 OHMS | MATERIAL: | SEE NOTES | DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: <u>+</u> 1/64 ANGULAR: X° <u>+</u> 1°0' | UNLESS O |
|-----------------------|--|--------------------------|---|---|---|
| FREQ. RANGE: VSWR: | DC TO 40.0 GHz. 1.40:1 MAX. DC TO 18.0 GHz. | FINISH: | SEE NOTES | DECIMAL: .X ±.030 | 1) ALL DIMENSIONS A 2) ALL DIMENSIONS A 3) BREAK CORNERS 4) CHAM. 1ST & LAST |
| | 1.60:1 MAX. DC TO 40.0 GHz. | SURFACE A | AREA: N/A PER ASME Y14.5M - 1994 | | 5) SURFACE ROUGH 6) DIA.'S ON COMMO |
| INSERTION LOSS: | 2.13dB MAX. DC TO 40.0 GHz. | | PROPRIETARY | | DRAWN: |
| | | IS THE SOLE ANY REPRO | IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED. | | CHECKED: |
| | | | | | APPROVED |



| | | | - |
|---------|---|-----------|--------------|
| SEE PDM | S | CALE: 4:1 | SHEET 1 OF 1 |
| | | | |