# **Mini Mighty Punch**

## [ Cheval ]

### **Precision Punch for Professional Results**



Cheval Mini Mighty hand punch is an essential addition to every workshop.

- Stripper plate and back gauge to ensure precision punching.
- Heavy duty steel construction with tough scratch resistant powder coat finish.
- Easy to change and align punches.

Perfect companion to enable your work on our System SA and PF-19 enclosures.

Part Number: ACCMMP1500

#### **Specifications**

#### **Largest Tool Dimension**

■ Rectangle 5x10 mm
■ Round 10 mm

Maximum Punch Force (P\_) 1,500 kgf

#### Maximum Materials Thickness (in mm.)\*

Materials	Punch		
Materials	Rectangle 3x7	Round 4.0	
Aluminium	3.0	3.5	
Zinc	2.5	3.0	
Copper	1.6	2.5	
Brass	1.6	2.5	
Steel	1.2	1.8	
Stainless Steel	0.9	1.2	

<sup>\*</sup> Based on punch sizes specified. Other punches can be used, refer to maximum materials calculation in Users Guide.

#### Overall Dimension (WxLxH)

Mini Mighty Punch
 Box
 365x110x110 mm

#### Weight

Net weightGross weight1.7 kg2.2 kg

#### Contents of Kit

Item	Description	QTY.	Image
1	Mini Hand Punch Body	1	
2	Punch Holder	1	•
3	Punch Tip 3.1 Rectangle 3x7 mm 3.2 Round 4.0 mm	2 1 1	
4	Die Holder	1	
5	Die 5.1 Rectangle 3x7 mm 5.2 Round 4.0 mm	2 1 1	
6	Stripper	1	
7	Back Gauge	1	
8	Handle Extension Tube	1	0. TH
9	Handle	1	
10	Table Clamp	1	Ĵ
11	Pin 6 mm	1	<b>1</b>
12	Pin 8 mm	1	

For more information about Mini Mighty Punch, please contact:

Cheval Electronic Enclosure Co., Ltd.

Email: commce@chevalgrp.com Tel: +662 315 1504-5

www.chevalgrp.com