


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

FCI P/N (NOTE 1)	"A" (NOTE 1)
56866-YXXX	XXX

COMPONENTS		
ITEM	QTY.	DESCRIPTION
1	4	SC CONECTOR KIT, 3mm, MM-127
2	"A"	CABLE, 3mm ZIP, MM-62.5/900
3	2	HEAT SHRINK TUBING, 1/4" O.D.
4	A/R	IDENTIFICATION LABEL (SEE NOTE 5)



SPECIFICATIONS	
INSERTION LOSS	0.5dB MAX
RETURN LOSS	N/A
FIBER PROTRUSION	50nm MAX
APEX OFFSET	45um MAX
FIBER UNDERCUT	SEE TELECORDIA GR-326

- NOTES:
- FCI PART NUMBER CONSISTS OF DWG NO, A DASH, AND A SUFFIX YXXX WHERE Y IS THE UNIT OF LENGTH (Y=M IS METERS AND Y=F IS FEET) AND WHERE XXX IS THE LENGTH "A".
(EX. 57666-F004 IS 4FT IN LENGTH)
 - CBL CERTIFIED TO IEC 60794-2.
 - CONTINUITY A-A & B-B.

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	NOMINALS ONLY			projection	title		
A	V12383	JRW	1/7/02		UNLESS NOTED				CA, DAV, SC-SC, 3ZIP-62 A-A; B-B		
B	V20731	JRW	4/16/02	angles				 mm	product family FIBER OPTICS		code
				dr	J. WITMER	1/7/02	size		dwg no	sheet	
				engr	S.K. CLARK	1/7/02	scale		A4	56866	1 of 1
				chr	S.K. CLARK	1/7/02	N/A				
				appd	S.K. CLARK	1/7/02					
sheet index	revision sheet										

cage code
22526

ACAD

PDM: Rev:B

STATUS Released

Printed: Apr 02, 2008