## 25ft F-TYPE RG-6 Shielded Coaxial Cable, 18 AWG (M60-025F)



## Product Overview

Commonly used for your cable TV, satellite, TV antenna, and broadband internet, this RG-6 coaxial cable provides a quality and superior transmission. Constructed from 75 Ohm coaxial cable with gold-plated F-type connectors, this cable provides a reliable and durable connection. The cable is fully shielded to reduce noise interference that can distort picture quality and covered with a flexible PVC jacket for easy installation.

## Features:

- Works with your cable TV, satellite, TV antenna, and broadband internet
- Gold-plated connector provides reliable connection and transmission
- Fully shielded to reduce interference
- Flexible PVC jacket
- Available in 3, 6, 12, 25, 50, 100 ft. lengths

Specifications: Model: M60-025F Length: 25 ft. Color: Black Weight: 0.75 lbs Connector A: F-Type Male Connector B: F-Type Male Connector: 18 AWG. RG-6/U CCS + 16/5/0.12 CCA Braid