

100W Replacement

3000K

Soft White

90+ CBI

Damp Rated

LED PAR38 LAMP


Model No. EP38-12W5000cec-2

LED *EP38-12W5000cec-2* delivers superior brightness, valuable energy savings, long lasting performance and true color perception. These PAR38 LED spot bulbs are ideal for task lighting due to its uniform *soft white light (3000K) and replace conventional 100 Watt incandescent light bulbs. Enjoy features such as: Instant on, dimming options, energy efficient, 90+CRI, and damp rated.



Electrical Specifications






CRI	Luminous Efficacy	Power Factor	Input Current	Base	Lamp Lifespan	Estimated Yearly Cost
90+	88 lm/W	0.9	0.1 A	E26	25,000 Hrs.	\$ 1.44


Mechanical Specifications

Rating	Operational Temperature	Inner Box QTY.	Master Box QTY.	Dimensions(in.)	UPC Code
Wet Rated	N/A	2 pcs	20 pcs	4.72"(ø) x 5.07"(H)	811174034513

Product Dimensions

Product Photometric Data





Euri Lighting İ A Division of IRTRONIX Inc.

20900 Normandie Avenue Suite B Torrance, CA 90502 | Tel: 888.743.5766 | Fax: 310.787.1166 | www.eurilighting.com ©2021 Euri Lighting. All Rights Reserved