SPECIFICATIONS:

Insulation Resistance: $500M\Omega$ min. at 500V DC Withstanding Voltage: 250Vrms for 1min

Voltage Rating: 5Vrms DC Current Rating: 0.5A

Contact Resistance: 100mΩ max. at 20mV max.

Operating Temp.: - 25°C ~ +85°C

Mating Cycle: 3,000 times

MATERIALS AND FINISH:

· Contacts: PB

· Metal Shell: Stainless Steel


· Insulator: LCP

FEATURES:

- · Clam-Shell locking mechanism
- R/A standard SMT mount
- · RoHS and REACH Compliant

PART NUMBER:

FUS008U-9000-0





OUTLINE DIMENSIONS (mm):

