

MQDMC-403-M24

► SINGLE-ENDED CORDSETS



Euro-Style Male Quick Disconnect Cable

4-pin Straight Connector: 2 Wire 20 AWG on pins 2 and 4

1 m (3 ft) in Length

Nickel-plated brass coupling nut

PVC jacketed cable

Part Number: 812760

SPECIFICATIONS

Number of Contacts	4
Number of Connectors	1
Cable Jacket Material	PVC
Cable Jacket Color	Black
Connector Body Material/Color	PUR Black
Cordset Length (m)	1
Trunk Length (m)	No Trunk
Shield/No Shield	No Shield
Coupling Material/Color	Nickel Plated Brass
Maximum Temp. (°C)	105
Current Rating (A)	4.0
Minimum Temp. (°C)	-40
Voltage Rating (V)	250 V ac/dc

IP Rating	IP67
Primary Connector Type	EURO
Primary Coupling Method	M12 Single Key
Primary Gender	Male
Primary Orientation	Straight
Primary Number of Conductors	2
Primary AWG	20
Secondary Connector Type	Flying Leads
Feature: Hazardous Area	No
Oil/Grease Resistant	No



Banner Engineering Corp. | 9714 Tenth Avenue North | Minneapolis, MN 55441 | United States of America