
## **PRODUCT DATA DRAWING**



## **MATERIAL:**

- CONNECTORS: 2.92mm FEMALE BULKHEAD (SF1521-60045)
  - 2.92mm MALE (SF1511-60069)
- CABLE: FLEXIBLE Ø.047 CABLE (200-70-214)
- SHRINK TUBING: M23053/5

## **PERFORMANCE:**

IMPEDANCE: FREQ. RANGE: 50 OHMS DC TO 40.0 GHz

MATERIAL: SEE NOTES FINISH: SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X* ±1*0' V*X' ±15' DECIMAL: .X ±.030 .XX ±.010	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING 3) BREAK CORNERS & EDGES 005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN 005 T.I.R. 7) REMOVE ALL BURRS		Amphenol WWW.svmicrowave.com		
SURFACE AREA: N/A	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994			<sup>TITLE:</sup> 2.92mm FEMALE BULKHEAD TO 2.92mm MALE 12" Ø.047 CABLE		
THE INFORMATION CONTAINED IN THIS DRA		DRAWN:	SJ 02/25/22	ASSEMBLY		
IS THE SOLE PROPERTY OF SV MICROWAVE ANY REPRODUCTION IN PART OR AS A WHC WITHOUT THE WRITTEN PERMISSION OF		CHECKED:	SEE PDM	SIZE DWG. NO.	7015-1	1098
SV MICROWAVE, INC IS PROHIBITED.		APPROVED:	SEE PDM	SCALE: 4:1		SHEET 1 OF 1

REVISION HISTORY					
REV	DESCRIPTION	DATE	APPROVED		
01	PRELIMINARY	02/22	SEE PDM		
02	PRELIMINARY	04/22			