
PRODUCT DATA DRAWING

	REVISION HISTORY			
	REV	DESCRIPTION	DATE	APPROVED
	01	PRELIMINARY	02/22	
02 F		PRELIMINARY	04/22 SEE PD	



COMPONENTS:

CONNECTORS: 2X 1.85mm MALE (SF3311-60002)

FLEXIBLE Ø.047 CABLE (200-70-214) CABLE:

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: FREQ. RANGE: 50 OHMS DC TO 65.0 GHz

				SV P/N	UAL
				7033-0035	6.000
				7033-0036	12.000
TERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIE	:D	Amphenol

	MATERIAL:	SEE NOT	ES	DIMENSIONS ARE I FRACTIONAL: +1/6	
	FINISH:	SEE NOT	ES	DECIMAL: .X ±.	
	SURFACE AREA: N/A			.XXX ± INTERPRET DIMEN PER ASME Y14.5M	
	PROPRIETARY				
	THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		THIRD ANG		
			+		

CTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' :IMAL: X ±.030	1) ALL DIMENSIONS ARE IN INCHES (MILLIMETE 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA: 5 ON COMMON CENTERS TO BE CONCE
ERPRET DIMENSIONS AND TOLERANCES ASME Y14.5M - 1994	WITHIN .005 T.I.R. 7) REMOVE ALL BURRS

CENTRIC DRAWN: SLE PROJECTION BFB 02/25/2 CHECKED: SEE PDM

APPROVED:

SEE PDM

	www.symicrowave.com	
TITLE:	1.85mm MALE TO 1.85mm	
	MALE Ø.047 CABLE	

SHEET 1 OF 1

22	ASSEMBLY		
M	SIZE B	DWG. NO.	7033-0035-0036

SCALE: 1:4