



Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are equipped to handle varying loads and are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications			
Gearhead Type:	Planetary	No-Load Speed:	118 rpm (+/- 10%)
Motor Type:	Carbon - Brushed	No-Load Current:	<300 mA
Rated Voltage:	24V DC	Stall Torque:	50 kg.cm
Rated Speed:	96 rpm	Max. Power:	15 W
Rated Torque:	9.25 kg.cm	Max. Efficiency:	37%
Termination Style:	Lead Wires (18AWG)		

