


**SPECIFICATIONS:**

Insulation Resistance: 1,000MΩ min. at 500V DC  
 Withstanding Voltage: 500Vrms for 1min  
 Voltage Rating: 5V DC  
 Current Rating: 0.5A  
 Contact Resistance: 100mΩ max. at 20mV max.  
 Operating Temp.: - 40°C ~ +85°C  
 Mating Cycle: 3,000 times

**PART NUMBER:**
**FPS009-2913-0**

**MATERIALS AND FINISH:**

- Contacts: PB
- Metal Shell: Stainless Steel
- Insulator: LCP

**FEATURES:**

- Card-detection switch
- Stand-Off from PCB = 1.80mm
- Stand-Off provides additional PCB design space
- RoHS and REACH Compliant


**OUTLINE DIMENSIONS (mm, With Card Detection Switch):**
