MICRO CONNECTORS®

7ft Cat6A UTP Ethernet Patch Cable (E09-007BL)



CAT 6A 10G UTP PATCH CABLE BLUE COLOR

- High performance CAT 6A 24 AWG Ethernet patch cable is perfect for connecting computers with devices such as routers, switches, patch panels and more.
- Cat6a cable can support 10 Gigabit data transmission up to 100 meters.
- Provide tighter twists to improve alien cross-talk performance.
- RJ45 connectors with 50-micron gold-plated contacts ensure clear transmission by eliminating signal loss due to corrosion.
- Snagless molded boot is designed to protect the locking tab of the RJ45 connector when plugging and unplugging.
- Our Cat6a cables are certified to handle Gigabit Ethernet with a bandwidth of up to 600 MHz.
- 100% pure copper wires are compliant with EIA/TIA standard by UL and ETL.
- RoHS compliant.

