




THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN CHOGORI PERSONNEL WITHOUT AUTHORIZATION FROM CHOGORI CORP.

| | | | | | | | | | |
|----------------|--------|-----------------------------|-----------------------|------|--------|-------------|-----------------|-----|------------|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | | |
| CUSTOMER No. : | REV. : | CATEGORY | IN LINE WITH THE TYPE | PAGE | REV. : | ECN&ECR No. | DESCRIPTION | DSN | DATE |
| | | | YES NO | | C1 | NA | Initial Drawing | XU | 2022.07.18 |
| | | NEW ENERGY VEHICLE PRODUCTS | | | | | | | |
| | | INDUSTRIAL PRODUCTS | √ | | | | | | |
| | | RoHS | √ | | | | | | |
| | | REACH | | | | | | | |
| | | Halogen-Free | | | | | | | |
| | | CALIFORNIA 65 | | | | | | | |



P/N: 22002635-01

SPECIFICATIONS:

- 1.INSULATION RESISTANCE : 10MΩ@500VDC/0.01S.
- 2.VOLTAGE RATING : 600V.
- 3.CURRENT RATING : 10A.
- 4.OPERATION TEMPERATURE : -10℃~+105℃.
- 5.WATERPROOF IPX7(MATED).
- 6.RoHS COMPLIANT.

| 4 | 900-00101-00087 | A/C | M | UL1015 18AWG PVC 105℃ 600V RED OD2.8 |
|------|-----------------|-----|------|--|
| 3 | 900-00101-00032 | A/C | M | UL1015 18AWG PVC 105℃ 600V BLACK OD2.8 |
| 2 | 504-00049-00 | A/C | M | ADHESIVE HEAT SHRINK TUBE OD3.2 |
| 1 | 22002635-01 | 1 | PC | STANDARD SERIES 2PIN PANEL MOUNT WITH FEMALE PIN(4 LOCKS -501) |
| ITEM | PART NO | QTY | UNIT | DESCRIPTION |

MATERIAL OF BILL

| | | |
|--------------------------------------|------------|--|
| UNIT: mm | | DESCRIPTION: STANDARD SERIES 2PIN PANEL MOUNT WITH FEMALE PIN(4 LOCKS -501) L=500MM |
| 未注线性和角度尺寸公差 UNSPECIFIED TOLERANCE | SCALE: 1:1 | SHEET: 1 OF 1 |
| GB/T 1804-M | REV.: C1 | SIZE: A4 ASME Y14.5-2009 |

CHOGORI[®]
深圳乔合里科技股份有限公司

| | | | | | |
|-----------|----------------|------------------|----|--------------|--|
| PART No.: | 11C03622051306 | DRAWN BY: | XU | TECHNICS: | |
| MATERIAL: | | PROOFREADED BY: | | QUALITY: | |
| MOLD No.: | | CHECKED BY: | | APPROVED BY: | |
| | | STANDARDISATION: | | | |