



THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN CHOGORI PERSONNEL WITHOUT AUTHORIZATION FROM CHOGORI CORP.

1	2	3	4	5	6	7	8		
CUSTOMER No. :	REV. :	CATEGORY	IN LINE WITH THE TYPE	PAGE	REV. :	ECN&ECR No.	DESCRIPTION	DSN	DATE
			YES NO						
		NEW ENERGY VEHICLE PRODUCTS			C1	NA	Initial Drawing	XU	2022.05.26
		INDUSTRIAL PRODUCTS	√	1	C2	NA	Change The Length To 1000mm	XU	2022.06.24
		RoHS	√						
		REACH							
		Halogen-Free							
		CALIFORNIA 65							



P/N: 22003133-01-001

**SPECIFICATIONS:**

- 1.INSULATION RESISTANCE: 10MΩ@500VDC/0.01S.
- 2.VOLTAGE RATING: 300V.
- 3.CURRENT RATING: 5A.
- 4.OPERATION TEMPERATURE: -10℃~+80℃.
- 5.WATERPROOF IPX7(MATED).
- 6.RoHS COMPLIANT.

<b>C2</b>	2	900-00301-00031	1.06	M	UL2464 3*20AWG+AB VW-1 PVC 80℃ 300V BLACK OD5.5
	1	22003133-01-001	1	PC	STANDARD SERIES 3PIN MALE CONNECTOR WITH MALE PIN(4 LOCKS,MOLDING,-501)
ITEM		PART NO	QTY	UNIT	DESCRIPTION

**MATERIAL OF BILL**

UNIT: mm		DESCRIPTION: STANDARD SERIES 3PIN MALE CONNECTOR WITH MALE PIN(4 LOCKS,MOLDING,-501) L=1000MM		
未注线性角度尺寸公差 UNSPECIFIED TOLERANCE		SCALE: 1:1	SHEET: 1 OF 1	
GB/T 1804-M	REV.: C2	SIZE: A4	ASME Y14.5-2009	

**CHOGORI**<sup>®</sup>  
深圳乔合里科技股份有限公司

PART No.:	11C03622051307	DRAWN BY:	XU	TECHNICS:	
MATERIAL:		PROOFREAD BY:		QUALITY:	
MOLD No.:		CHECKED BY:		APPROVED BY:	
		STANDARDISATION:			

A B C D E F