



P/N: 23003635-01

SPECIFICATIONS:

- 1.INSULATION RESISTANCE: 10MΩ@500VDC/0.01S.
- 2.VOLTAGE RATING: 600V.
- 3.CURRENT RATING: 20A.
- 4.OPERATION TEMPERATURE: -10℃~+105℃.
- 5.WATERPROOF IPX7(MATED).
- 6.RoHS COMPLIANT.

5		6		7		8	
REV.	ECN NO.	DATE	SIGN	DESCRIPTION			
C1	NA	2022/05/28	XU	First Version			

5	900-00101-00149	A/R	M	UL1015 14AWG PVC 105℃ 600V GREEN OD3.5
4	900-00101-00148	A/R	M	UL1015 14AWG PVC 105℃ 600V WHITE OD3.5
3	900-00101-00062	A/R	M	UL1015 14AWG PVC 105℃ 600V BLACK OD3.5
2	504-00016-00	A/R	M	HEAT SHRINK TUBE OD4.0
1	23003635-01	1	PC	MIDDIE SERIES 3PIN PANEL MOUNT WITH FEMALE PIN(4 LOCKS,-511)
No.	Material No.	Q'ty	Unit	Material Description

Material List

ITEM NO.	11C03622051409	DRAWN BY	XU	DATE	2022/05/28
DWG NO.	11C03622051409	CHECKED BY		DATE	
CUSTOMER NO.		REV.		APPROVED BY	

UNIT:mm	TITLE	
未注线性和角度尺寸公差 UNSPECIFIED TOLERANCE	MIDDIE SERIES 3PIN PANEL MOUNT WITH FEMALE PIN(4 LOCKS,-511) L=500MM	
SCALE N/A	SHEET 1 of 1	
REV. C1	SIZE A4	* Inspection Item

CHOGORI[®]
Chogori Technology Co., Ltd

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN CHOGORI PERSONNEL WITHOUT AUTHORIZATION FROM CHOGORI CORP.