
PRODUCT DATA DRAWING

REVISION HISTORY				
REV	DESCRIPTION	DATE	APPROVED	
01	PRELIMINARY	02/22		
02	PRELIMINARY	04/22	SEE PDM	



MATERIAL:

CONNECTORS: 2.92mm FEMALE BULKHEAD (SF1521-60025)

2.92mm MALE (SF1511-60071)

FLEXIBLE Ø.085 CABLE (200-70-139) CABLE:

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS FREQ. RANGE:

DC TO 40.0 GHz

DIMENSIONS ARE IN INCHES TOLERANCES:			
FRACTIONAL: ±1/64 ANGULAR: X° ±1°0'			
X°X' ±15' DECIMAL: .X ±.030			

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING,
3) BREAK CORNERS & EDGES .005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63-MIL-STD-10.
6) DIA'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R.
7) REMOVE ALL BURRS INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994 THIRD

D ANGLE PROJECTION	DRAWN:	SJ 02/25/22
	CHECKED:	SEE PDM
	APPROVED:	SEE PDM

UNLESS OTHERWISE SPECIFIED

MICROWAVE

2.92mm FEMALE BULKHEAD TO 2.92mm MALE 12" Ø.085 CABLE ASSEMBLY

SIZE B	DWG. NO.	7015-	5-1099	
SCALE: 4:1			SHEET 1 OF 1	