AcuPanel 15

15" Rugged Panel PC - IP65

OUTDOOR PANEL PC











WIRELESS CONNECTIVITY

















AcuPanel 15

15" Rugged Panel PC - IP65

OUTDOOR PANEL PC



FULLY CUSTOMIZABLE | 3 YEAR WARRANTY

SYSTEM

SCREEN SIZE 15 TFT ACTIVE

MATRIX LED

PROCESSOR INTEL J1900 OR i5 CPU

BRIGHTNESS 350 NITS
MEMORY UP TO 32 GB
LCD TYPE LED BACKLIT

TOUCH SCREEN CAPACITIVE MULTI TOUCH

OR RESISTIVE

POWER INPUT
OPERATING SYSTEM
STORAGE
9 - 36V DC POWER INPUT
WINDOWS 7/10 OR LINUX
SATA TYPE III - HDD/SSD

ENVIRONMENTAL

OPERATING TEMP -20°C TO 60°C

(-4°F TO 140°F)

STORAGE TEMP -30°C TO 70°C

(-22°F TO 158°F)

RELATIVE HUMIDITY <96% (NON CONDENSING)

CERTIFICATIONS CE

CE, FCC CLASS A, ISO CERTIFIED

IP RATING IP65 - FRONT PANEL

NEMA RATING NEMA4

1/0

SERIAL PORT UP TO 4x RS232 OR RS485

LAN UP TO 2x RJ45 PORT GBE

USB UP TO 4x USB 2.0

UP TO 4x USB 3.0 WIFI 802.11 A/B/G/N

WIRELESS 4G/LTE (OPTIONAL)

MECHANICAL

MOUNTING SUPPORT PANEL-MOUNT

/VESA - MOUNT 100 x 100 mm

.

CONSTRUCTION ALUMINUM ALLOY

WEIGHT 5 KG - 11 LBS **DIMENSIONS** 15" x 11.8" x 2"

37.5 x 30 x 5.8 CM

MODEL NUMBERS

AcuPanel 15 MDL # AP15J1900 / AP15i5