Micro Air Pump Motor

MAP-AM-265

DC Mini-Motors

APPLICATIONS


Blood Pressure monitor for Arm type



SPECIFICATIONS

Items	Specifications	Conditions
Rated Voltage	6.0V	
Voltage Range	5.0~7.0V	
Pressing Time	11.5sec or less	Time to add pressure from 0 to 300mmHg to a tank of 500cc by rated voltage (DC 6V).
Current Consumption	430mA or less	Maximum current during adding pressure from 0 to 300mmHg to a tank of 500cc by rated voltage (DC 6V).
Leakage of Air	3.0mmHg/min or less	Decrease of pressure at 30 second after stop pumping to a tank of 500cc up to 40±10mmHg and 300 ± 10mmHg.
Maximum Pressure	400mmHg or more	
Noise	55.0dB or less	Noise at 30cm from the pump.

DIMENSIONS



Unit: mm

Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.