



LED DLC6S-2040*ej*

Part #: EFDLC6DM/I/12W/1050/120D/50K/JB/E Fixture Class: 6" Slim Fixed



Product Description

LED DLC6S-2040ej, delivering unbeatable brightness, valuable energy savings, and long-lasting performance, this LED downlight is the perfect choice for recessed lighting. Energy Star Certified and JA8 Compliant, this ultra-slim downlight uses minimal watts to output maximum lumens in Bright White (4000K) color temperature. IC-rated, dimmable, and with 90+ CRI, this 6-inch LED downlight guarantees unbeatable performance for 50,0000 hours. See Euri Lighting DLC6S-2000ej for pleasing Soft White (3000K).










Estimated Energy Cost: \$1.44 per year







Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
12 W	120V/60Hz	900 lm	120°	NA cd	4000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base	Lamp Lifespan
90	75 lm/W	0.9	0.1 A	Junction Box	50,000 Hrs.

Product Features



Dimmable



Abutted & Covered




No Housing Required




Damp Rated

Product Dimensions



Product Photometric Data



Euri Lighting | A Division of *IRTRONIX* Inc.