

# Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/12AH - 1283121

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Replacement battery, VRLA-AGM, 2x12 V DC, 12 Ah



### **Key Commercial Data**

Packing unit	1 pc
GTIN	4 063151 488130
GTIN	4063151488130
Custom tariff number	85072080
Country of origin	China

#### Technical data

#### **Dimensions**

Width	200 mm
Height	153 mm
Depth	100 mm

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (storage/transport)	-20 °C 40 °C
Ambient temperature (charge)	0 °C 40 °C
Ambient temperature (discharge)	-20 °C 50 °C
Max. permissible relative humidity (operation)	≤ 95 %
Degree of pollution	2



# Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/12AH - 1283121

### Technical data

#### General

Protection class	III
Degree of protection	IP20
Degree of pollution	2
Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations.
Battery type	BB Battery BP 12-12FR
Battery technology	VRLA-AGM
Latest startup date (battery only)	12 Months (0 °C 20 °C)
Latest startup (battery only) - range	9 Months 12 Months (20 °C 30 °C)
	6 Months 9 Months (30 °C 40 °C)
Accumulator module service life (according to Eurobat)	6 (20 °C)

### Input data

Input voltage	2x 12 V
Nominal capacity	12 Ah

### **Environmental Product Compliance**

China RoHS	Environmentally Friendly Use Period = 8
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

#### Classifications

### eCl@ss

eCl@ss 11.0	27059090
-------------	----------

## Approvals

#### Approvals

Approvals

GOST-R

Ex Approvals



# Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/12AH - 1283121

### **Approvals**

Approval details



Phoenix Contact 2021 © - all rights reserved http://www.phoenixcontact.com