## 2.2W White LED Tape Light Kit, Standard Output

#### **SPECIFICATION:**

Input Voltage	12 VDC
Wattage	2.2 W/ft
Output	2700K - 208 lm/ft
	3000K - 214 lm/ft
	5200K - 230 lm/ft
CRI	90+
Dimmable	0-10V, ELV, MLV
Max. Run Length	16 ft
Field Cuttable	3.9" cut points
Beam Angle	120°
LED Tape Operating Temp.	-13°F to 140°F
LED Tape Warranty	5 year limited*
LED Tape Lifetime	50,000 hours
LED Tape Adhesive	3M™ VHB mounting adhesive on back
LED Tape Dimensions	0.39" W x 0.08" H (10mm x 2.0mm)
Incl. Power Supply	120VAC to 12VDC, 72W Capacity
IP Rating	IP20 - dry locations only















### Applications:

- Indoor Signage
- Indirect Lighting
- Accent Lighting
- Undercabinet Lighting
- Furniture Accents

## **INCLUDED IN KIT**



T300-XXK-12V-R16 16FT TAPELIGHT REEL


1 OF EACH



P72W12V 12V POWER SUPPLY

1 OF EACH





2 OF EACH



# 2.2W White LED Tape Light Kit, Standard Output

#### **SPECIFICATION:**

