# 2.2W White LED Tape Light, 16 Ft. Reel

### **SPECIFICATION:**

| Input Voltage   | 24 VDC                                   |
|-----------------|--|
|                 |  |
| Wattage         | 2.2 W/ft                                 |
| Output          | 2700K - 208 lm/ft                        |
|                 | 3000K - 214 lm/ft                        |
|                 | 5200K - 230 lm/ft                        |
| CRI             | 90+                                      |
| Dimmable        | 0-10V, ELV, MLV                          |
| Max. Run Length | 16 ft                                    |
| Field Cuttable  | 3.9" cut points                          |
| Beam Angle      | 120°                                     |
| Operating Temp. | -13°F to 140°F                           |
| Warranty        | 5 year limited*                          |
| Lifetime        | 50,000 hours                             |
| Adhesive        | 3M™ VHB mounting adhesive on back        |
| Dimensions      | 0.39" W x 0.08" H (10mm x 2.0mm)         |
| Power Supply    | Compatible with all 24VDC power supplies |






#### Applications:

- Indoor Signage
- Indirect Lighting
- Accent Lighting
- Undercabinet Lighting
- Furniture Accents

## **DIMENSIONS**



# RECOMMENDED ACCESSORIES



TAPE-TO-TAPE BLOCK CONNECTOR

**BLOCK-TW-SC** 



TAPE-TO-WIRE BLOCK CONNECTOR

**BLOCK-TT-SC** 



TAPE-TO-TAPE GRIPPER CONNECTOR

**GRIPPER-TT-SC** 



TAPE-TO-WIRE GRIPPER CONNECTOR

**GRIPPER-TW-SC** 

