EVEREADY® READYFLEX Floating Lantern

GPLN451

Bright and dependable, the *EVEREADY*® READYFLEX Floating Lantern is a great choice for everyday needs. Featuring long lasting LED technology, this ergonomic solution also shines up to 5X brighter than standard LED technology. With READYFLEX technology, users also receive the flexibility to operate with either 2 or 4 batteries. Users can be ready for everyday or emergency situations with just 2 D batteries, or they can extend runtime for days on 4 D batteries. With hours and hours of clear, uniform light, users will be prepared for a wide variety of outdoor and indoor tasks.



Provides 80 Lumens of Light



Provides Run Time of 140 Hours



Shines Light on Objects up to 175 Meters Away



IPX 4 Water Resistant

DESIGN BENEFITS

- ✓ Floats for easy retrieval
- ✓ READYFLEX technology enables operation on 2 or 4 D cell batteries
- ✓ Non-slip grip

LIGHT AND POWER SOURCE

- √ Features LED Technology
- ✓ Operates on either 2 or 4 D batteries

CERTIFICATES AND COMPLIANCE





Tested according to ANSI/NEMA FL1 Standards.

EVEREADY SUPER HEAVY DUTY Results based on: Carbon Zinc (4 batteries)

PERFORMANCE BENEFITS

- ✓ Powerful beam
- ✓ Up to 5X brighter than standard LED technology
- ✓ Long run time

SPECIFICATIONS

Weight Excluding Batteries:

250 Grams / 8.8 Ounces

Dimensions:

177mm x 125mm x125m / 7" x 5" x 5"

NUMBER OF OPERATING MODES: 1

Mode	Lumens (lm)	Runtime (h)	Beam Distance (m
On (2 EVEREADY» SUPER HEAVY DUTY)	80	70	175
On (4 EVEREADY» SUPER HEAVY DUTY)	80	140	175
On (2 EVEREADY» A95 Alkaline)	65	200	150
On (4 EVEREADY» A95 Alkaline)	65	400	150