

Remote transmitter - M2M TC CLOUD VZW - 1107519

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)

Provides a secure, cellular VPN connection to a machine network. Utilizes the Verizon cellular network.



Your advantages

- Secure VPN connection
- ☑ Cost-effective remote access for OEM's and system integrators.
- ☑ Can be shipped to location, eliminating personnel travel costs.
- ☑ Can be used onsite to monitor multiple systems.
- Simple method to connect to devices remotely using standard RJ45 Ethernet connector.

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	3,240.000 g
Country of origin	United States

Technical data

Note

Trade restriction	The products are offered exclusively for export outside the EU and the European Economic Area.	
Monitoring		
Supply voltage	120 V AC (15 ft. NEMA 5-15 power cable included)	
General data		
Installation location	Portable	
Degree of protection	NEMA 4X	
Ambient conditions		
Ambient temperature (operation)	-25 °C 60 °C	
Environmental Product Compliance		
REACh SVHC	Lead 7439-92-1	



Remote transmitter - M2M TC CLOUD VZW - 1107519

Articles in set

Power supply unit - UNO-PS/1AC/24DC/ 30W - 2902991



Primary-switched UNO POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/30 W

Thermomagnetic device circuit breaker - UT 6-TMC M 2A - 0916605



Thermomagnetic circuit breaker, 1-pos., for DIN rail mounting

Router - TC CLOUD CLIENT 1002-4G VZW - 2702887



Industrial VPN gateway for mGuard Secure Cloud, IPsec communication via 4G (LTE), Verizon Wireless (US), 2-port switch, 1 digital input, 1 digital output

Phoenix Contact 2020 © - all rights reserved http://www.phoenixcontact.com