

Remote transmitter - M2M RS4000 ATT - 2404230

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Provides a secure, cellular VPN connection to a machine network. Utilizes the AT&T cellular network.

Your advantages

- ☑ Secure VPN connection
- Can be shipped to location, eliminating personnel travel costs.
- ☑ Can be used onsite to monitor multiple systems.
- ☑ Simple method to connect to devices remotely using standard RJ45 Ethernet connector.

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	1.000 g
Country of origin	Germany

Technical data

Note	
Trade restriction	The products are offered exclusively for export outside the EU and the European Economic Area.
Monitoring	
Supply voltage	120 V AC (15 ft. NEMA 5-15 power cable included)
General data	
Installation location	Portable
Degree of protection	NEMA 4X
Ambient conditions	
Ambient temperature (operation)	-25 °C 60 °C
Environmental Product Compliance	
REACh SVHC	Lead 7439-92-1



Remote transmitter - M2M RS4000 ATT - 2404230

Articles in set

Power supply unit - UNO-PS/1AC/24DC/ 30W - 2902991



Primary-switched UNO POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/30 W

Thermomagnetic device circuit breaker - UT 6-TMC M 2A - 0916605



Thermomagnetic circuit breaker, 1-pos., for DIN rail mounting

Security Appliance - TC MGUARD RS4000 4G ATT VPN - 1010463



Security appliance, version for AT&T (US), WAN and 4G mobile network interface, SD card slot, 10 VPN tunnels, intelligent firewall with full scope of functions, router with NAT/1:1 NAT, optional CIFS Integrity Monitoring, 4 port Managed Switch

Phoenix Contact 2020 @ - all rights reserved http://www.phoenixcontact.com