







## **Metric table**

Dimensions in: millimeters - inches ٦ **d<sub>1</sub>** Thread  $d_2$ d<sub>3</sub>  $d_4$ h k M 5 5.3 8 20 14 12 .79 .55 .21 .47 .31 M 6 24 16 6.7 14 10 .63 .39 .94 .55 .26 M 8 30 20 8.7 17 12 1.18 .79 .34 .67 .47 M 10 36 28 11 20 14 .55 1.42 1.10 .43 .79 40 M 12 32 13 24 16 1.26 .94 .63 1.57 .51

## Specification

- Steel
- Tensile strength class 5
- Blackened finish

 Stainless steel European Standard No. 1.4305 (AISI 303) Matte shot-blasted finish

RoHS compliant

## Information

2

NI

GN 6303.1 quick release knurled nuts are used in such applications where the nut has to be completely removed after the releasing operation and mounted again rapidly for re-clamping.

The nut is tilted over the threaded spindle. When in position, the nut is brought into a straight position for mating of the two threads on the nut and spindle. The nut will then have to be turned only by a fraction of a rotation to achieve clamping.

Functional safety exists only if the clamping surface lies at a right angle to the threaded bolt.

see also...

• Quick Release Star Knobs GN 6336.3

How to order (Steel) GN 6303.1-M8	1	Thread d <sub>1</sub>
How to order (Stainless steel)	1	Thread d1
	2	Material