


REV.	ECN NO.	DATE	BY	DESCRIPTION
01		Sep/03/2020	Aine Li	RELEASED



WIRE RUN LIST							
AWG	CONN 1	COLOR	CONN 2	AWG	CONN 1	COLOR	CONN 2
42	1	LIGHT GREEN	1	42	21	LIGHT GREEN	21
	2	LIGHT GREEN	2		22	LIGHT GREEN	22
	3	LIGHT GREEN	3		23	LIGHT GREEN	23
	4	LIGHT GREEN	4		24	LIGHT GREEN	24
	5	LIGHT GREEN	5		25	LIGHT GREEN	25
	6	LIGHT GREEN	6		26	LIGHT GREEN	26
	7	LIGHT GREEN	7		27	LIGHT GREEN	27
	8	LIGHT GREEN	8		28	LIGHT GREEN	28
	9	LIGHT GREEN	9		29	LIGHT GREEN	29
	10	LIGHT GREEN	10		30	LIGHT GREEN	30
	11	LIGHT GREEN	11		31	LIGHT GREEN	31
	12	LIGHT GREEN	12		32	LIGHT GREEN	32
	13	LIGHT GREEN	13		33	LIGHT GREEN	33
	14	LIGHT GREEN	14		34	LIGHT GREEN	34
	15	LIGHT GREEN	15		35	LIGHT GREEN	35
	16	LIGHT GREEN	16		36	LIGHT GREEN	36
	17	LIGHT GREEN	17		37	LIGHT GREEN	37
	18	LIGHT GREEN	18		38	LIGHT GREEN	38
	19	LIGHT GREEN	19		39	LIGHT GREEN	39
	20	LIGHT GREEN	20		40	LIGHT GREEN	40
					SHELL	LIGHT GREEN	SHELL

ITEM	QTY	DESCRIPTION
7.	A/R	3M TAPE
6.	A/R	UV GLUE
5.	A/R	KAPTON TAPE
4.	4	GROUND BAR WGB009C W0.5
3.	2	SHELL, HRS: DF36A-40P-SHL
2.	2	CONN., 40P, HRS: DF36-40P-0.4SD
1.	A/R	HOOK-UP WIRE, UL1354, COAX42#, OD=0.33

- NOTES:
- TESTING SPEC.:
COND. RESISTANCE: 3Ω MAX.
INSUL. RESISTANCE: 10MΩ MIN.
TESTING VOLTAGE: 200V DC
 - BOTH CONN. NEED TO MOLD WITH UV GLUE.
 - RoHS COMPLIANCE.

THIS DRAWING CONTAINS CONFIDENTIAL INFORMATION AND IS THE PROPERTY OF SINBON ELECTRONICS CO., LTD. IT MAY NOT BE USED OR ITS CONTENTS COPIED OR DISCLOSED TO A THIRD PARTY WITHOUT PRIOR WRITTEN CONSENT AND IS TO BE RETURNED PROMPTLY UPON REQUEST BY SINBON ELECTRONICS CO., LTD.

CUSTOMER : DigiKey		REV. : N/A		 SINBON Electronics Co., Ltd.	
CUSTOMER P/N : N/A		DRA. : Sep/03/2020 Aine Li			
UNLESS OTHERWISE SPECIFIED TOLERANCE :		CHK. : Sep/03/2020 Kevin Qiu		PART NUMBER : DF36A40PP-UL42S200	
1 ~ 10 : ±1 11 ~ 30 : ±2 31 ~ 50 : ±3 51 ~ 200 : ±5 201 ~ 400 : ±7 > 401 : ±10 ANGLES : ±1°		APR. : Sep/03/2020 Kevin Qiu		REV. : 01	
		SIZE : A3	UNIT : mm	SCALE : NONE	SHEET : 1 of 1