
# Eagle Eyes - AIH


7th Generation Intel® Xenon® E3/Core™ S Series (FCLGA1151 Socketed) Box Computer, 2x RJ45 Gbe, 4xRJ45 Gbe/PoE



Plug 2(dB) 50 Ω 161 mm

# Eagle Eyes - AIH

7th Generation Intel® Xenon® E3/Core™ S Series (FCLGA1151 Socketed) Box Computer, 2x RJ45 Gbe, 4xRJ45 Gbe/PoE



#### I/O Chart

| Model Name | DP | DVI-D | VGA | GbE (RJ45) | GbE / PoE (RJ45) | DIO        | USB 3.0 | RS-232 | RS-232/422/485 | M.2 2280 NVMe | Internal 2.5" Disk Bay |
|------------|----|-------|-----|------------|------------------|------------|---------|--------|----------------|---------------|------------------------|
| AIH        | 2  | 1     | 1   | 2          | 4                | 16-bit DIO | 6       | 4      | 2              | 0             | 3                      |

## **Order Information**

Part Number

AIH-7700t-8G-2.5S256G-P216B12

Intele 7th Gen Kaby Lake S (KBL-S) platform, LGA 1151 Socketed i7-7700T CPU, 2x DP, 1x DVI, 1x VGA, 2x GbE (RJ45), 4x BgE/PoE (RJ\$%), 6x USB 3.0, 1x RS-232/422/485, 1x RS-232, 32-Bit DIO, 3x Internal SATA ports for 2.5" SSD, DIN Rail, 8GB RAM, 256 GB 2.5" SATA SSD, 160W Power Adapter & Cord.

## Packing List

- 1
- Eagle Eyes AlH Embedded Box PC x 1 AC-DC Power Adapter (24V/160W) with pitch 5.0mm 3-pin terminal block plug
- 3. AC-DC Power Cord YP-12/YC-12, plug type B, American (USA)

4. Six anti-slide rubber pads