

ø 57mm BLDC Motor

3-Phase Brushless

MOT-I-81576-CS

Online ID#: BLDC-J52

BLDC-J57-47-24-4800-CS


Our BLDC Motors are a high quality solution providing excellent speed and torque output with superior reliability and control.


With endless performance combinations, we have a fully tailored gear motor solution for you.


Contact Us for alternative solutions!


Specifications	
Motor Type:	Brushless (BLDC)
Rated Voltage:	24V DC
Rated Speed:	4,000 rpm
Rated Torque:	1.12 kg.cm
Rated Current:	3.2 A
Termination Style:	Lead Wires (20AWG)

No-Load Speed:	4,800 rpm (+/- 10%)
No-Load Current:	< 0.65 A
Back EMF:	5 V/krpm
Torque Constant:	0.49 kg.cm/A
Max. Power:	112 W
Construction:	4 Pole









ISL Products International Ltd. • 572 Walt Whitman Rd., Suite 100 • Melville, NY 11747 • T 516-937-3475 • www.islproducts.com