

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IT'S SUBSIDIARIES. POSITRONIC BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.


 SK9116

 DATE REV
 REVISION RECORD
 APP DR CK

 11-29 NC
 ECO 28708
 RCW YK TK







## NOTES:

1. MATERIALS AND FINISHES:

HOOD, COVER AND INSERT: COMPOSITE, CONDUCTIVE VOLUME RESISTIVITY (1.0 OHM—cm MAX.), UL94V—0.

ATTENUATION: 40+ DECIBELS.

JACKSCREWS: STEEL WITH ZINC PLATE WITH CHROMATE SEAL.

CABLE CLAMPS: STEEL, NICKEL PLATE.

CABLE CLAMP SCREWS: BRASS, ZINC PLATE WITH CHROMATE SEAL.

COVER SCREWS: STAINLESS STEEL, PASSIVATED.

2. DIMENSIONS ARE IN INCHES [MILLIMETERS].



			SCALE NI TO	DRAWN BY	YK
DECIMAL TOL.	D SERIES		N.T.S.	APPROVED BY	RCW
$\pm 0.015 [0.38]$	D37000Z00				
	DATE	DRAWING NUMBER			REV.
ANGULAR TOL. $\pm 5^{\circ}$	11-29-07	SKO	9116		