Click Connectors

for LED linear lighting | not to be used in wet locations

SIZE	ACTUAL WIDTH	PRODUCT COMPATIBILITY	DRIVER COMPATIBILITY	FLYING WIRE LEAD LENGTH
8MM	11.9mm / 0.46"	. T150, T300, TSHL5050-150,	only class 2 power unit	3", 6", 12", 24", 36", 60" or specify custom length (not available for TSPLICE connector)
10MM	14.1mm / 0.55"	TSHL2825 series, and TUB5630 series, T150RGB, T300RGB,		
14MM	19.55mm / 0.77"	T300RGBWW, T300RGBCW		



TCON-CL **TCONNECT**

single slide linear lighting connector to flying wire lead



TPWR-CL TPOWERCONNECT

linear lighting to power supply slide connector



TYCON-CL TYCONNECT

single slide linear lighting connector to 2 additional linear lighting runs



TYPWR-CL TYPOWERCONNECT

single power connector to 2-way split slide linear lighting connectors



TCOR-CL **TCORNER**

single slide linear lighting connector to additional linear lighting run




TSPL-CL **TSPLICE**

single connector for 2 runs of linear lighting (the top of the connector has a red dot)

ORDER

90° TURNS



		8mm	10mm	connected runs
TLCORNER	TLCOR-CL TLRGBCOR-CL	1.15" x 1.15" 29.21mm x 29.21mm	1.25" x 1.25" 31.75mm x 31.75mm	2
TTCORNER	TTCOR-CL TTRGBCOR-CL	1.75" x 1.15" 44.50mm x 29.21mm	2" x 1.25" 50.80mm x 31.75mm	3
TXCORNER	TXCOR-CL TXRGBCOR-CL	1.75" x 1.75" 44.50mm x 44.50mm	2" x 2" 50.8mm x 50.8mm	4