Splash Proof Centrifugal Fan

Centrifugal fans of IP54 and IP56 waterproof capability. For more information on IP rating, refer to p. 587. Related product: Splash Proof Fan p. 247, Centrifugal Fan p. 425, Splash Proof Blower p. 331, Oil Proof Fan p. 335

Model Numbering System Not every combination of the following codes or characters is available. Contact us for an available combination.

9W1T	M	48	P	4	Н	01	
Type name	Impeller size	Voltage	PWM control function	Thickness	Speed code	Individual customer's spec (2 to 3 digits)	

Bracket-mounted Splash Proof Centrifugal Fan

9B1W2T	Р	24	P	0	Н	001
Type name	Impeller size	Voltage	PWM control function	Thickness	Speed code	Individual customer's spec (3 digits)

Type name	9W1T	9W2T	9B1W2T			
Impeller size (mm)	G	J	М	N	Р	S
	ø175	ø133	ø100	ø150	ø221	ø225
Voltage (V)		48 48				
Thickness (mm)	0	1	4			
Speed code	69 min.	35 S	25 etc.			

How to Read Specifications (DC fan) The following is a sample. See respective product pages for detailed information.

Model no.	Rated voltage	Operating voltage range	Rated current	Rated input	Rated speed	Max. airflow		Max. static pressure		SPL	Operating temperature	Expected life
	[V]	[V]	[A]	[W]	[min ⁻¹]	[m³/min]	[CFM]	[Pa]	[inchH2O]	[dB (A)]	[°C]	[h]
9GA0412G7001	12	7 to 13.8	0.17	2.04	13100	0.36	12.7	192	0.77	42	-20 to +70	40000/60°C (70000/40°C)

Rated voltage This is the necessary voltage to drive the fan. E.g.) 12 VDC, 24 VDC, 48 VDC

Operating voltage range The voltage range over which fan operation is guaranteed.

Rated current The current when the fan is operating at rated voltage (at free air).

Rated input The power value when the fan is operating at rated voltage (at free air).

Rated speed \cdots The speed when the fan is operating at rated voltage (at free air).

Max. airflow The airflow at 0 Pa static pressure when the fan is operating at rated voltage. (Measured using the double chamber method)

Max. static pressure The static pressure at 0 m³/min airflow when the fan is operating at rated voltage. (Measured using the double chamber method)

SPL A-weighted sound pressure level (SPL) when the fan operates at the rated speed.

For the measurement method, see the Technical Materials section in the catalog.

Operating temperature The temperature range over which fan operation is guaranteed (Non-condensing).

Expected life Service life hours that 90% of bearings will survive without failing when continuously operated at the rated voltage and 60°C

temperature. Expected life at 40°C is for reference only.

For more information, please refer to the technical material section.