



MINIATURE CABLE TIES, 18 LB, 4 INCH, GREEN NYLON



- Easy color coding and identification
- Operating temperatures from -40° F to 185° F
- High tensile strength with the low insertion force



Main Information

Category:	Colors - 4" 18 lb Cable Ties
Per Case:	10,000, Sold in case quantities
Color / Material:	Green Nylon
Mil Spec Reference:	MS3367-4-5
Tensile Strength Pounds:	18
Tensile Strength Newtons:	80
Length inch:	4.12
Length mm:	104.77
Width inch:	0.09
Width mm:	2.41
Thickness Inch:	0.04
Thickness mm:	1.06
Max. Bundle Dia. Inch:	0.87
Max. Bundle Dia. mm:	22.22
Min. Bundle Dia. Inch:	0.06
Min. Bundle Dia. mm:	1.57
Max. Operating Temp. F:	185
Max. Operating Temp. C:	85
Min. Operating Temp. F:	-40
Min. Operating Temp. C:	-40
Min. Installation Temp. F:	-4
Min. Installation Temp. C:	-20
UL Listed:	UL Listed Type 21
Air Handling Approved:	UL & CSA AH-2 Rated
UL Material Flame Rating:	94 V-2
CSA Certified:	CSA Certified Type 21
CE Compliance:	Type 2
RoHS Compliant:	RoHS Compliant
Weight per bag:	0.9 lbs
Weight per case:	9 lbs
Country of Origin:	USA

PART NUMBER (S)	QUANTITY
AL-04-18-5-M	1000/bag

Documentation

- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Marketing Literature)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Reference Documents)
- Miniature Cable Ties, 18 lb, 4 inch, Green Nylon (Spec Sheet Drawing)

Solutions

- UL Approved
- DIY Retail

© 2023 Advanced Cable Ties, Inc.