
CONFIDENTIAL & PROPRIETARY INFORMATION

This document contains Confidential and Proprietary Information of Alliance LLC, and all design, manufacturing, reproduction, use, and sale rights of such information are expressly reserved

ALL DIMENSIONS ARE IN MM





5.00 ± .12

NOTES:

1. MAGNET PROPERTIES PER N-42SH:

Br: 12,900-13,200 G Hc: 11,900-12,600 Oe Hci: ≥20,000 Oe T max: 150 C

- 2. SUPPLED MAGNETIZED ACROSS THE DIAMETER
- 3. PARTS ARE NICKEL PLATED FOR 15hrs SALT SPRAY MIN

			4		
4		1	7	2	1
		V			
	CO	MPL	CH JAN	Т	

REV	DESCRIPTION	DATE	BY
В	Changed CAD, incl cert, 3D	2/08/14	ВТ

TOLERANCES (UNLESS OTHERWISE NOTED)				
DECIMAL METRIC X.XX = ± .01 X.X = ± .25 X.XXX= ± .005 X.XX= ± .13				
ANGLES ± .5°				
DO NOT SCALE DRAWING				

1450 CLARK DRIVE, VALPARAISO, INDIANA 46385						
DESCRIPTION: 10 mm x 5.0 mm DISC MAGNET						
SENSOR MAGNET		P/N: ALC1051				
GRADE: N-42SH	Drwg by: BT	REV LEVEL: B				
COATING: Nickel	Appr by: DV	Appr. Dated: 05-25-2013				

Alliance LLC