
CONFIDENTIAL & PROPRIETARY INFORMATION

This document contains Confidential and Proprietary Information of Alliance LLC, and all design, manufacturing, reproduction, use, and sale rights of such information are expressly reserved

ALL DIMENSIONS ARE IN MM





NOTES:

1. MAGNET PROPERTIES PER N-40SH:

Br: 12,600-12,900 G Hc: 11,500-12,200 Oe Hci: ≥20,000 Oe Tmax: 150 C

2. SUPPLIED MAGNETIZED THROUGH THE THICKNESS

3. PARTS ARE BLACK EPOXY COATED

		10	
	9		1
RE	ACI	H NT	

REV	DESCRIPTION	DATE	BY
В	Changed CAD, incl cert, 3D	2/14/14	ВТ

Alliance LLC 1450 CLARK DRIVE, VALPARAISO, INDIANA 46385

TOLERANCES
(UNLESS OTHERWISE NOTED)

DECIMAL METRIC
X.XX = ± .01 X.X = ± .25
X.XXX=± .005 X.XX=± .13

ANGLES
± .5°

 $\pm \ .5^{\circ}$ DO NOT SCALE DRAWING

DESCRIPTION: 4.0 mm x 1.5 mm DISC MAGNET						
SENSOR MAG	P/N: ALC4015					
GRADE: N-40SH	Drwg by: BT	REV LEVEL: B				
COATING: Epoxy	Appr by: DV	Appr. Dated: 11-21-2013				