
## CONFIDENTIAL & PROPRIETARY INFORMATION

This document contains Confidential and Proprietary Information of Alliance LLC, and all design, manufacturing, reproduction, use, and sale rights of such information are expressly reserved

## ALL DIMENSIONS ARE IN MM





## NOTES:

1. MAGNET PROPERTIES PER N-35SH:

Br: 11,800-12,200 G Hc: 10,800-11,500 Oe Hci: ≥20,000 Oe T max: 150 C

2. SUPPLIED MAGNETIZED ACROSS THE DIAMETER

3. PARTS ARE BLACK EPOXY COATED

			A		
0			1		۱
	`				
	R	EA!	CH IAN	r )	

REV	DESCRIPTION	DATE	BY
В	Changed CAD, incl cert, 3D	1/30/14	ВТ

## Alliance LLC 1450 CLARK DRIVE, VALPARAISO, INDIANA 46385

TOLERANCES (UNLESS OTHERWISE NOTED)

DECIMAL METRIC

X.XX =  $\pm$  .01 X.X =  $\pm$  .25

X.XXX=  $\pm$  .005 X.XX=  $\pm$  .13

ANGLES

+ .5°

⊥ .5					
DO NOT SCALE DRAWING					

DESCRIPTION: 5.0 mm x 2.5 mm DISC MAGNET						
SENSOR MAGNET		P/N: ALC5025				
GRADE: N-35SH	Drwg by: BT	REV LEVEL: B				
COATING: Epoxy	Appr by: DV	Appr. Dated: 05-15-2013				