
## CONFIDENTIAL & PROPRIETARY INFORMATION

This document contains Confidential and Proprietary Information of Alliance LLC, and all design, manufacturing, reproduction, use, and sale rights of such information are expressly reserved

## ALL DIMENSIONS ARE IN MM





## NOTES:

1. MAGNET PROPERTIES PER N-35SH:

Br: 11,800-12,200 G Hc: 10,800-11,500 Oe Hci: ≥20,000 Oe T max: 150 C

2. SUPPLIED MAGNETIZED ACROSS THE DIAMETER

3. PARTS ARE NICKEL PLATED

			N	
(4		1		1
Г				
	RE	AC PLIA	H NT	

REV	DESCRIPTION	DATE	BY
В	Changed CAD, incl cert, 3D	1/30/14	ВТ

## Alliance LLC 1450 CLARK DRIVE, VALPARAISO, INDIANA 46385

TOLERANCES
(UNLESS OTHERWISE NOTED)

DECIMAL METRIC
X.XX = ± .01 X.X = ± .25
X.XXX= ± .005 X.XX= ± .13

ANGLES

L F0

± .5	
NOT SCALE DRAWING	3

1100 025 4 4 4 51 4 7 2, 77 21 7 4 6 4 6 6 7, 11 7 4 7 4 7 6 6 6 6					
DESCRIPTION: 5.0 mm x 2.5 mm DISC MAGNET					
SENSOR MAGNET		P/N: ALC5025N			
GRADE: N-35SH	Drwg by: BT	REV LEVEL: B			
COATING: Nickel	Appr by: DV	Appr. Dated: 06-20-2013			