
CONFIDENTIAL & PROPRIETARY INFORMATION

This document contains Confidential and Proprietary Information of Alliance LLC, and all design, manufacturing, reproduction, use, and sale rights of such information are expressly reserved

ALL DIMENSIONS ARE IN MM





NOTES:

1. MAGNET PROPERTIES PER N-35SH:

Br: 11,700-12,200 G Hc: 11,000-11,600 Oe Hci: ≥20,000 Oe T max: 150 C

- 2. SUPPLIED MAGNETIZED THROUGH THE THICKNESS
- 3. PARTS ARE NICKEL PLATED FOR 15hrs SALT SPRAY MIN.

		1
(4		1
	REACH COMPLIANT	

REV	DESCRIPTION	DATE	BY
В	Changed CAD, incl cert, 3D	1/30/14	ВТ

1450 CLARK DRIVE, VALPARAISO, INDIANA 46385 **TOLERANCES** DESCRIPTION: 6.4 mm x 1.9 mm DISC MAGNET (UNLESS OTHERWISE NOTED) **DECIMAL METRIC** SENSOR MAGNET P/N: ALC6319 $X.XX = \pm .01$ $X.X = \pm .25$ $X.XXX = \pm .005 \ X.XX = \pm .13$ GRADE: N-35SH Drwg by: BT REV LEVEL: B **ANGLES** \pm .5 $^{\circ}$ Appr by: DV Appr. Dated: 03-15-2013 COATING: Nickel DO NOT SCALE DRAWING

Alliance LLC