

## CA-T2T2-5M-11/3P-R-BBG

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	AC charging cable, Plug type - charging point: Type 2, Plug type - vehicle side: Type 2, Charging power, max.: 11 kW, Number of phases: 3, Rated current: 20 A, Cable length: 5 m, Cable type: regular
Order No.	<a href="#">2754380000</a>
Type	CA-T2T2-5M-11/3P-R-BBG
GTIN (EAN)	4050118899115
Qty.	1 pc(s).

## CA-T2T2-5M-11/3P-R-BBG

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	2,160 g
------------	---------

## Temperatures

Storage temperature	-40 °C...70 °C	Humidity at storage temperature	5 - 95% rel. humidity
Operating temperature	-30 °C...50 °C	Operating temperature, min.	-30 °C
Operating temperature, max.	50 °C		

## Material data

Max. relative humidity during storage	95 %	Operating temperature, max.	50 °C
Operating temperature, min.	-30 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

## System requirements

Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)
----------------------------------	---

## Features

Protection degree	IP54
-------------------	------

## Housing

Protection degree	IP54
-------------------	------

## Approvals and norms

Approvals	IEC 62196-1, IEC 62196-2, EN 50620
-----------	---------------------------------------

## Classifications

ETIM 6.0	EC002897	ETIM 7.0	EC002897
ETIM 8.0	EC002897	ECLASS 9.0	27-14-47-05
ECLASS 9.1	27-14-47-05	ECLASS 10.0	27-14-47-05
ECLASS 11.0	27-14-47-05	ECLASS 12.0	27-14-47-05

## Downloads

User Documentation	<a href="#">Safety notes</a> <a href="#">Safety notes</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**CA-T2T2-5M-11/3P-R-BBG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

