

**CA-T2T2-10M-22/3-R-BBG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |   |
|------------|---|
| Version    | AC charging cable, Plug type - charging point: Type 2, Plug type - vehicle side: Type 2, Charging power, max.: 22 kW, Number of phases: 3, Rated current: 32 A, Cable length: 10 m, Cable type: regular |
| Order No.  | <a href="#">2791310000</a>  |
| Type       | CA-T2T2-10M-22/3-R-BBG  |
| GTIN (EAN) | 4064675070788   |
| Qty.       | 1 pc(s).  |

Creation date May 1, 2023 9:06:33 PM CEST

## CA-T2T2-10M-22/3-R-BBG

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 3,500 g |
|------------|---------|

## Temperatures

|                             |                |                                 |                       |
|-----------------------------|----------------|---------------------------------|-----------------------|
| Storage temperature         | -40 °C...70 °C | Humidity at storage temperature | 5 - 95% rel. humidity |
| Operating temperature       | -30 °C...55 °C | Operating temperature, min.     | -30 °C                |
| Operating temperature, max. | 55 °C          |                                 |                       |

## Material data

|                                       |        |                             |       |
|---------------------------------------|--------|-----------------------------|-------|
| Max. relative humidity during storage | 95 %   | Operating temperature, max. | 55 °C |
| Operating temperature, min.           | -30 °C | Storage temperature, max.   | 70 °C |
| Storage temperature, min.             | -40 °C |                             |       |

## System requirements

|                                  |   |
|----------------------------------|---|
| Type of communication to vehicle | Control Pilot (CP),<br>Proximity Pilot / Plug<br>Present (PP) |
|----------------------------------|---|

## Features

|                   |      |
|-------------------|------|
| Protection degree | IP54 |
|-------------------|------|

## Housing

|                   |      |
|-------------------|------|
| Protection degree | IP54 |
|-------------------|------|

## Approvals and norms

|           |                                       |
|-----------|---------------------------------------|
| Approvals | IEC 62196-1, IEC<br>62196-2, EN 50620 |
|-----------|---------------------------------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002897    | ETIM 7.0    | EC002897    |
| ETIM 8.0    | EC002897    | ECLASS 9.0  | 27-14-47-05 |
| ECLASS 9.1  | 27-14-47-05 | ECLASS 10.0 | 27-14-47-05 |
| ECLASS 11.0 | 27-14-47-05 | ECLASS 12.0 | 27-14-47-05 |

## Downloads

|                    |  |
|--------------------|--|
| User Documentation | <a href="#">Safety notes</a>             |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |

**Data sheet**

**CA-T2T2-10M-22/3-R-BBG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

