

**CA-T2T2-10M-11/3-R-BBG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	AC charging cable, Plug type - charging point: Type 2, Plug type - vehicle side: Type 2, Charging power, max.: 11 kW, Number of phases: 3, Rated current: 20 A, Cable length: 10 m, Cable type: regular
Order No.	<a href="#">2791330000</a>
Type	CA-T2T2-10M-11/3-R-BBG
GTIN (EAN)	4064675070825
Qty.	1 pc(s).

## CA-T2T2-10M-11/3-R-BBG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 3,560 g

### Temperatures

Storage temperature	-40 °C...70 °C	Humidity at storage temperature	5 - 95% rel. humidity
Operating temperature	-30 °C...55 °C	Operating temperature, min.	-30 °C
Operating temperature, max.	55 °C		

### Material data

Max. relative humidity during storage	95 %	Operating temperature, max.	55 °C
Operating temperature, min.	-30 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

### System requirements

Type of communication to vehicle Control Pilot (CP),  
Proximity Pilot / Plug  
Present (PP)

### Features

Protection degree IP54

### Housing

Protection degree IP54

### Approvals and norms

Approvals IEC 62196-1, IEC  
62196-2, EN 50620

### Classifications

ETIM 6.0	EC002897	ETIM 7.0	EC002897
ETIM 8.0	EC002897	ECLASS 9.0	27-14-47-05
ECLASS 9.1	27-14-47-05	ECLASS 10.0	27-14-47-05
ECLASS 11.0	27-14-47-05	ECLASS 12.0	27-14-47-05

### Downloads

User Documentation [Safety notes](#)  
Catalogues [Catalogues in PDF-format](#)

**Data sheet**

**CA-T2T2-10M-11/3-R-BBG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

