

CH-W-S-A22-P7.5-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Wallbox, With attached 7.5 m cable and type 2 plug, Mobile App
Order No.	2911220000
Type	CH-W-S-A22-P7.5-E
GTIN (EAN)	4099986532199
Qty.	1 pc(s).

CH-W-S-A22-P7.5-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	150 mm	Depth (inches)	5.905 inch
Height	433 mm	Height (inches)	17.047 inch
Width	268 mm	Width (inches)	10.551 inch
Net weight	6,550 g		

Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-30 °C...50 °C
Operating temperature, min.	-30 °C	Operating temperature, max.	50 °C

Material data

Max. relative humidity during storage	95 %	Operating temperature, max.	50 °C
Operating temperature, min.	-30 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C		

Performance specification

Performance specification	Input voltage type	AC
	Input voltage	400 V
	Input current, max.	32 A
	Charging power, max	22 kW
	Adjustment accuracy	1 A
	Charging current adjustable	Yes
	Charging current, min	6 A

System requirements

Connection system	With attached 7.5 m cable and type 2 plug	Type of communication to vehicle	Control Pilot (CP), Proximity Pilot / Plug Present (PP)
Charge mode	Mode 3	Protection class	I
Surge voltage category	III	Pollution severity	3

Features

Protection degree	IP54	Type of status indicator	RGB LED
Welding detection	Yes	Failure shutdown	Yes
Failure shutdown method	All-pole	DC - residual current detection integrated	Yes
DC - residual current	6 mA	Type of residual current detection to be provided by the installation	RCD Type A
User authentication	Yes	Mobile App available	Yes
User authentication type	Mobile App	Integrated energy measuring MID conform	Yes
Communication integrated	Yes	Supported protocols	Modbus RTU, Modbus TCP, OCPP 1.6 (J)

Interfaces

Wifi frequency	2,4 GHz	Wifi Standard	802.11 b/g/n
Bluetooth module	Bluetooth Low Energy (BLE)	Ethernet ports	1
Digital inputs	1 (12 V / 6 mA)	Digital outputs	1 (12 V / 100 mA)
Type of protocol of serial interface	RS485		

CH-W-S-A22-P7.5-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Assembly

Installation	Wall mounting, Stand Mounting
--------------	-------------------------------

Included in delivery

Included in delivery	Drilling template, Instruction sheet, Mounting screws, Assembly dowels
----------------------	--

Housing

Operating altitude	≤ 3000 m	Housing main material	PC
Protection degree	IP54	Colour	black, Anthracite, grey
Impact resistance	IK10 in accordance with IEC 62262		

Approvals and norms

Approvals	IEC 61851-1, IEC 61851-2 1-2, IEC 62196-1, IEC 62196-2, EN 50620, EN 301 489-1, EN 301 908-1, EN 301 511, EN 300 328, EN 300 330 v.2.1.1, EN 62368-1, EN 55011
-----------	--

Connection data (supply cable)

Conductor cross-section, max.	16 mm ²
-------------------------------	--------------------

Classifications

ETIM 6.0	EC002883	ETIM 7.0	EC002883
ETIM 8.0	EC002883	ECLASS 9.0	27-14-47-01
ECLASS 9.1	27-14-47-01	ECLASS 10.0	27-14-47-01
ECLASS 11.0	27-14-47-01	ECLASS 12.0	27-14-47-01

Downloads

Approval/Certificate/Document of Conformity	CE declaration
Engineering Data	Installationsvideo AC SMART Installation Video AC SMART AC SMART Modbus registers
Software	Firmware – Current Bluetooth Firmware AC SMART Firmware – Current Firmware AC SMART Firmware – Current WiFi Firmware AC SMART Firmware – Archive Firmware files AC SMART Firmware – Release notes Current firmware AC SMART
Tender specification	Ausschreibungstexte
User Documentation	Broschüre Wallbox AC SMART, AC Ladekabel, Basiskomponenten Brochure EV charging box AC SMART, AC charging cables, Basic components Abnahmeprotokoll AC SMART MANUAL AC SMART (DE, EN) Application notes – Instructionsheet AC SMART
Catalogues	Catalogues in PDF-format

Data sheet

CH-W-S-A22-P7.5-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

