
L6999-9
ACTUAL
SIZE

TUNING ROTOR




FIG. 1

FIG. 2

SPECIFICATIONS		FILE: AIROUT
THREADS	PRE-TORQUED & LUBRICATED	
FINISH	JOHANSON STANDARD CHROMATE CONVERSION	
MOUNTING	JMC TAP P/N 7053 TAP DRILL 3/64 (.0469)	
BRASS STRUCTURE		

APPLICATIONS:
FOR HIGH Q VARIABLE REACTANCE TUNING OF MICROWAVE CAVITIES, FILTERS, AND OTHER RESONANT STRUCTURES.

JMC P/N	FIG.	A	B
L6999-0	1	.500	.385
L6999-1	1	.315	.200
L6999-2	1	.170	.055
L6999-3	1	.190	.075
L6999-4	1	.230	.115
L6999-5	1	.260	.145
L6999-6	1	.285	.170
L6999-7	1	.200	.085
L6999-8	1	.215	.100
L6999-9	2	.170	.090
L6999-10	1	.375	.260
L6999-11	1	.155	.040
L6999-12	2	.120	.040
L6999-13	1	.271	.156
L6999-14	1	.285	.170

R	9/30/15	RJV	RJV 9/30/15 MAI	001347	
LEVEL	DATE	DRN.	CHK.	APP.	ECN

REVISIONS

DRN.	CHK.	APP.	SCALE
RJV	RJV	MAI	16" \approx 1"
DATE	DATE	DATE	.XX \pm .015
01/10/07	01/16/07	01/17/07	.XXX \pm .005



JOHANSON MANUFACTURING CORPORATION
ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION